




ISO CAMERA OECF TEST CHART 80:1

TRANSPARENCY



Contrast ratio 80 : 1

For measuring procedures see ISO 14524.

| step | density (ISO) | density chart |
|------|---------------|---------------|
| 1 | 2.00 | |
| 2 | 1.66 | |
| 3 | 1.39 | |
| 4 | 1.17 | |
| 5 | 0.97 | |
| 6 | 0.81 | |
| 7 | 0.66 | |
| 8 | 0.53 | |
| 9 | 0.41 | |
| 10 | 0.30 | |
| 11 | 0.19 | |
| 12 | 0.10 | |
| 13 | 0.74 | |

Densities based on light source = 0
 Measuring equipment : Techkon RT 120 Densitometer

Frechen: