

TE253



www.image-engineering.de

Acceptance protocol

SN:	JJ_XXX-TE253-XXXXXXXXXX
Order Confirmation:	ABxxxx
Date:	
Operator:	

Reflectances of the gray patches*

Patch	Reference reflectance	Measured reflectance	Deviation	Optical density
1 (white)	0,89			0,05
2	0,85			0,07
3	0,80			0,09
4	0,76			0,12
5	0,71			0,15
6	0,67			0,17
7	0,62			0,20
8	0,58			0,24
9	0,53			0,27
10	0,49			0,31
11	0,44			0,35
12	0,40			0,40
13	0,35			0,45
14	0,31			0,51
15	0,26			0,58
16	0,22			0,66
17	0,18			0,76
18	0,13			0,89
19	0,09			1,07
(black) 20	0,04			1,40
Edge	0,05			1,30
Background	0,20			0,70



*Measured with X-Rite eXact

https://www.image-engineering.de/content/products/charts/IE_reference_data_accuracy.pdf